

GALEA

5070PJP125P30-12

EAN 4031582378665
Order number 00770900



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Galea
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	162 mm
Overall width	66 mm
Overall weight	0.521 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	30 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races
Offset	40 mm
Swivel radius	102.5 mm
Swivel interference	205 mm
Dome diameter	59 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	12 mm

GALEA

5070PJP125P30-12

EAN 4031582378665
Order number 00770900



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

