

KAPPA FLEX

9758ITP200P63 SH92A

EAN 4031582443646



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa flex
Type	Fixed caster
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	992.08 lb
Load capacity at 3.7 mph	661.39 lb
Electric conductive	no
Stainless	no
Load capacity Static	1984.16 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	10.24 in
Overall weight	10.36 lb

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	With spring

WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	5.59 in
Plate width	4.37 in
Plate hole length (Minimum)	3.9 in
Plate hole length (Maximum)	4.41 in
Plate hole width (Minimum)	2.91 in
Plate hole width (Maximum)	3.27 in
Plate hole diameter	0.5 in