

OMIKRON TWIN

9950FTP300P68

EAN 4031582316827
Order number 00800999



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Omikron twin
Type	Swivel castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 2.5 mph	13227.72 lb
Load capacity at 3.7 mph	8818.48 lb
Load capacity Static	19841.58 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	16.34 in
Overall width	10.71 in
Overall weight	147.52 lb

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	11.81 in
Tread width	3.15 in
Body width	3.15 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Color	Transparent coating
Offset	3.15 in
Swivel radius	9.76 in
Swivel interference	19.53 in
	✓
Dome diameter	9.84 in

FITTING

Fitting type	Rectangular plate
Plate length	10.63 in
Plate width	9.84 in
Plate hole length (Maximum)	8.27 in
Plate hole width (Maximum)	9.06 in
Plate hole diameter	0.67 in

OMIKRON TWIN

9950FTP300P68

EAN 4031582316827
Order number 00800999



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

