

# ANIKA

5920UAI065P41-38X38

EAN 4031582456080



BETTER MOBILITY. BETTER LIFE.

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Anika
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	77 mm
Overall width	39.5 mm
Overall weight	0.075 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	65 mm
Tread width	11 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	55.5 mm
Swivel interference	111 mm
Dome diameter	18 mm

## FITTING

Fitting type	Square plate
Plate length	38 mm
Plate width	38 mm
Plate hole length (Maximum)	27 mm
Plate hole width (Maximum)	27 mm
Plate hole diameter	5 mm



PRODUCT INFORMATION

# ANIKA

5920UAI065P41-38X38

EAN 4031582456080



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---



Interzum  
Award