

AGILA

2470DIK100R07-Ø21,5-24

EAN 4031582328226
Order number 00064228



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	135 mm
Overall width	60 mm
Overall weight	0.959 kg

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	38 mm
Swivel radius	88 mm
Swivel interference	176 mm
Dome diameter	60 mm

FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	22 mm
Expander fitting (Maximum)	24 mm
Hint	Please indicate required tube innerdiameter when ordering.

AGILA

2470DIK100R07-Ø21,5-24

EAN 4031582328226
Order number 00064228



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

