

# AGILA

2470DYK075R07-Ø24-27

EAN 4031582340747



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	121.25 lb
Electric conductive	Yes
Stainless	no
Load capacity Static	242.51 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	4.06 in

## HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Blue passivated
Offset	0.94 in
Swivel radius	2.42 in
Swivel interference	4.84 in

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black, electric-conductive
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Hardness of tread (A)	80 Shore A

## FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	0.94 in
Expander fitting (Maximum)	1.06 in
Hint	Please indicate required tube innerdiameter when ordering.

# AGILA

2470DYK075R07-Ø24-27

EAN 4031582340747



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

