

# AGILA

2470PJO075R47-24-27

EAN 4031582324815  
Order number 00031540



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Load capacity Static	330.69 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	4.06 in
Overall weight	0.75 lb

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	0.94 in
Swivel radius	2.42 in
Swivel interference	4.84 in

## FITTING

Fitting type	Synthetic expander, square
Expander fitting (Minimum)	0.94 in
Expander fitting (Maximum)	1.06 in
Hint	Please indicate required tube innerdiameter when ordering.

# AGILA

2470PJO075R47-24-27

EAN 4031582324815  
Order number 00031540



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

