

AGILA

2470DIK150P30-11

EAN 4031582010374
Order number 00006708



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 220.46 lb |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 7.28 in |
| Overall width | 2.36 in |
| Overall weight | 3.01 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, non-marking |
| Bearing | Cone ball bearing |
| Wheel color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 5.91 in |
| Tread width | 1.26 in |
| Body width | 1.26 in |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Color | Blue passivated |
| Offset | 1.77 in |
| Swivel radius | 4.72 in |
| Swivel interference | 9.45 in |
| Dome diameter | 2.36 in |

FITTING

| | |
|--------------------|--|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.43 in |
| Hint | Castors can be mounted with standard screws of any length. |

AGILA

2470DIK150P30-11

EAN 4031582010374
Order number 00006708



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

