

AGILA

2477PJO075P40

EAN 4031582050370
Order number 00003359



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Load capacity Static	330.69 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.94 in
Overall width	1.69 in
Overall weight	0.66 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	0.94 in
Swivel radius	3.15 in
Swivel interference	6.3 in
Dome diameter	1.69 in

FITTING

Fitting type	Square plate
Plate length	2.36 in
Plate width	2.36 in
Plate hole length (Minimum)	1.5 in
Plate hole length (Maximum)	1.89 in
Plate hole width (Minimum)	1.5 in
Plate hole width (Maximum)	1.89 in
Plate hole diameter	0.25 in

AGILA

2477PJO075P40

EAN 4031582050370
Order number 00003359



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

