

# KAPPA

9688ITP125P63 CL67

EAN 4031582316452  
Order number 00802070



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Kappa                         |
| Type                        | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 1102.31 lb                    |
| Load capacity at 3.7 mph    | 881.85 lb                     |
| Load capacity Static        | 2204.62 lb                    |
| Temperature range (Minimum) | 14 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 6.69 in                       |
| Overall width               | 3.86 in                       |
| Overall weight              | 3.81 lb                       |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Aluminum               |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Wheel color           | Honey yellow (RAL1005) |
| Threadguards          | Without threadguard    |
| Diameter              | 4.92 in                |
| Tread width           | 1.97 in                |
| Body width            | 1.97 in                |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## HOUSING

|               |                                  |
|---------------|----------------------------------|
| Material      | Cast iron, or iron forged, heavy |
| Fork shape    | Broad, reinforced                |
| Color         | Blue passivated                  |
|               | ✓                                |
| Dome diameter | 3.78 in                          |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 5.31 in           |
| Plate width                 | 4.33 in           |
| Plate hole length (Minimum) | 2.95 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Minimum)  | 2.95 in           |
| Plate hole width (Maximum)  | 4.13 in           |
| Plate hole diameter         | 0.43 in           |

# KAPPA

9688ITP125P63 CL67

EAN 4031582316452  
Order number 00802070



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

