

GALEA

5077YGH125R05-22X40 7001/7042 SCREWED

EAN 4031582354287



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Galea
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric conductive	✓
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	162 mm
Overall width	65 mm
Overall weight	0.656 kg

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing
Tread color	Traffic grey A (RAL7042)
Wheel color	Traffic grey A (RAL7042)
Threadguards	With threadguard
Diameter	125 mm
Tread width	30 mm
Axle hole diameter	0 mm
Hub length	0 mm
Body width	30 mm
Hardness of tread (A)	90 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races
Colour	Silver grey (RAL7001)
Offset	40 mm
Swivel radius	135 mm
Swivel interference	270 mm
Dome diameter	59 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	22 mm
Bolt length	40 mm

GALEA

5077YGH125R05-22X40 7001/7042 SCREWED

EAN 4031582354287



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

