

AGILA

2477PJO125R05-28 M8/19

EAN 4031582302028
Order number 00029315



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Agila |
| Type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 163 mm |
| Overall width | 60 mm |
| Overall weight | 1.075 kg |

WHEEL

| | |
|-----------------------|-----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 125 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Colour | Blue passivated |
| Offset | 41 mm |
| Swivel radius | 131 mm |
| Swivel interference | 262 mm |
| Dome diameter | 60 mm |

FITTING

| | |
|------------------------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 28 mm |
| Bolt length | 45 mm |
| Bolt thread position | 19 mm |
| Bolt mounting holes quantity | 2 |

AGILA

2477PJO125R05-28 M8/19

EAN 4031582302028
Order number 00029315



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

