

# GALEA STAINLESS

5087PJC100P30-10

EAN 4031582383683



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Galea stainless               |
| Type                        | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 100 kg                        |
| Stainless                   | ✓                             |
| Load capacity Static        | 200 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 139 mm                        |
| Overall width               | 66 mm                         |
| Overall weight              | 0.476 kg                      |

## WHEEL

|                       |                                   |
|-----------------------|-----------------------------------|
| Body material         | Polypropylene                     |
| Tread material        | Thermoplastic rubber              |
| Bearing               | Precision ball bearing, stainless |
| Threadguards          | With threadguard                  |
| Diameter              | 100 mm                            |
| Tread width           | 30 mm                             |
| Hardness of tread (A) | 87 Shore A                        |

## HOUSING

|                     |   |
|---------------------|---|
| Material fork       | Polyamide                               |
| Fork shape          | Closed                                  |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Offset              | 40 mm                                   |
| Swivel radius       | 128 mm                                  |
| Swivel interference | 256 mm                                  |
| Dome diameter       | 59 mm                                   |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 10 mm     |

# GALEA STAINLESS

5087PJC100P30-10

EAN 4031582383683



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

