

# AGILA STAINLESS

7475PJH050P30-12,3

EAN 4031582351088



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Agila stainless                |
| Type                        | Swivel castor with wheel brake |
| Standard                    | EN12530 - Devices Castors      |
| Load capacity at 1.8 mph    | 110.23 lb                      |
| Stainless                   | ✓                              |
| Load capacity Static        | 220.46 lb                      |
| Temperature range (Minimum) | -4 °F                          |
| Temperature range (Maximum) | 140 °F                         |
| Overall height              | 2.72 in                        |
| Overall weight              | 0.38 lb                        |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | With threadguard     |
| Diameter              | 1.97 in              |
| Tread width           | 0.75 in              |
| Hardness of tread (A) | 85 Shore A           |

## HOUSING

|                     |                         |
|---------------------|-------------------------|
| Material            | Stainless steel, medium |
| Fork shape          | Broad                   |
| Swivel bearing      | Two ball races          |
| Offset              | 0.94 in                 |
| Swivel interference | 3.86 in                 |
|                     | polyamide               |

## FITTING

|                    |  |
|--------------------|--|
| Fitting type       | Bolt hole  |
| Bolt hole diameter | 0.48 in  |
| Hint               | Castors can be mounted with standard screws of any length. |

# AGILA STAINLESS

7475PJH050P30-12,3

EAN 4031582351088



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

