

AGILA US

2677PJP5X1.25P30-13

EAN 4031582435962



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila US
Housing type	Swivel castor with total lock
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	125 kg
Load capacity Static	250 kg
Overall height	156 mm

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	126 mm
Tread width	32 mm
Axle hole diameter	10 mm
Hardness of tread (A)	77 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Offset	37 mm
Swivel radius	119 mm
Swivel interference	237 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

AGILA US

2677PJP5X1.25P30-13

EAN 4031582435962



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

