

# OMIKRON TWIN

9950FTP125P65

EAN 4031582316759  
Order number 00802882



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                       |
|-----------------------------|---------------------------------------|
| Product name                | Omikron twin                          |
| Housing type                | Swivel castor                         |
| Standard                    | similar EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 1500 kg                               |
| Load capacity at 6 km/h     | 1100 kg                               |
| Load capacity Static        | 2250 kg                               |
| Temperature range (Minimum) | -10 °C                                |
| Temperature range (Maximum) | 60 °C                                 |
| Overall height              | 205 mm                                |
| Overall width               | 189 mm                                |
| Overall weight              | 15.215 kg                             |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Casting                |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Wheel color           | Honey yellow (RAL1005) |
| Threadguards          | With threadguard       |
| Diameter              | 125 mm                 |
| Tread width           | 50 mm                  |
| Body width            | 50 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## HOUSING

|                     |  |
|---------------------|--|
| Material            | Iron forged, heavy                     |
| Fork shape          | Twin wheel housing                     |
| Swivel bearing      | Deep-groove ball thrust roller bearing |
| Colour              | Transparent coating                    |
| Offset              | 50 mm                                  |
| Swivel radius       | 123 mm                                 |
| Swivel interference | 246 mm                                 |
| Dome diameter       | 160 mm                                 |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 200 mm            |
| Plate width                 | 160 mm            |
| Plate hole length (Maximum) | 120 mm            |
| Plate hole width (Maximum)  | 160 mm            |
| Plate hole diameter         | 15 mm             |

# OMIKRON TWIN

9950FTP125P65

EAN 4031582316759  
Order number 00802882



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

