

# FOOTMASTER

FOOT MASTER GAGD-100-ASF-HUD

EAN 4031582495287  
Order number 00800103



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

## CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	310 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall height	150 mm
Overall width	118 mm
Overall weight	6.66 kg

## WHEEL

Bearing	Unmachined hub
Diameter	100 mm
Tread width	30 mm
Body width	30 mm

## HOUSING

Offset	30 mm
Swivel radius	84 mm
Swivel interference	168 mm
Dome diameter	104 mm

## FITTING

Plate length	112 mm
Plate width	112 mm
Plate hole length (Maximum)	92 mm
Plate hole width (Maximum)	92 mm
Plate hole diameter	9 mm

# FOOTMASTER

FOOT MASTER GAGD-100-ASF-HUD

EAN 4031582495287  
Order number 00800103



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

