

# KAPPA LOAD

9650FTP200P64 CL97

EAN 4031582314212  
Order number 00829771



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Kappa load
Type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1680 kg
Load capacity at 6 km/h	1400 kg
Load capacity Static	2800 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	255 mm
Overall width	140 mm
Overall weight	13.052 kg

## WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	200 mm
Tread width	80 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Colour	Zink-iron (transparent)
Offset	65 mm
Swivel radius	170 mm
Swivel interference	340 mm
Lubrication nipple	✓
Dome diameter	140 mm

## FITTING

Fitting type	Large rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Maximum)	140 mm
Plate hole diameter	15 mm

# KAPPA LOAD

9650FTP200P64 CL97

EAN 4031582314212  
Order number 00829771



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

