

# LINEA LOW HEIGHT

5940UAP100P30-12 LH RAL9002

EAN 4031582423440



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Linea low height
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	103 mm
Overall width	73 mm
Overall weight	0.447 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	20 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	32 mm
Swivel radius	88 mm
Swivel interference	180 mm
Dome diameter	41 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	12 mm



Deutscher Designer Club



Interzum Award



IF Design Award

# LINEA LOW HEIGHT




5940UAP100P30-12 LH RAL9002

EAN 4031582423440



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award