

LUMINA

A520POI042L51-8 CHROME/9011

EAN 4031582317268
Order number 00072826



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Lumina |
| Type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 66.14 lb |
| Load capacity Static | 132.28 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 1.93 in |
| Overall width | 1.5 in |
| Overall weight | 0.06 lb |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Tread color | Graphite black (RAL9011) |
| Wheel color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 1.65 in |
| Tread width | 0.24 in |
| Body width | 0.24 in |
| Hardness of tread (D) | 65 Shore D |

HOUSING

| | |
|---------------------|---------------------------------------|
| Material | Polypropylene |
| Fork shape | Twin wheel housing, closed, with dome |
| Swivel bearing | Stem, swiveling |
| Offset | 0.63 in |
| Swivel radius | 1.54 in |
| Swivel interference | 3.07 in |

FITTING

| | |
|--------------------|----------------------------|
| Fitting type | Blind hole for B10 fitting |
| Bolt hole diameter | 0.31 in |

PRODUCT INFORMATION

LUMINA

A520POI042L51-8 CHROME/9011

EAN 4031582317268
Order number 00072826



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

