

AGILA

2478UAP150P50

EAN 4031582302431



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila
Type	Fixed caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	7.28 in
Overall weight	1.83 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Hardness of tread (D)	40 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	3.03 in
Plate width	2.64 in
Plate hole length (Minimum)	2.2 in
Plate hole length (Maximum)	2.42 in
Plate hole width (Minimum)	1.83 in
Plate hole width (Maximum)	2.03 in
Plate hole diameter	0.33 in

AGILA

2478UAP150P50

EAN 4031582302431



BETTER MOBILITY. BETTER LIFE.

Product Drawings

