

AGILA

2470PIO125P30-11

EAN 4031582361100
Order number 00062870



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 176.37 lb |
| Load capacity Static | 352.74 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 6.3 in |
| Overall weight | 1.4 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Solid rubber, non-marking |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 4.92 in |
| Tread width | 1.26 in |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 1.61 in |
| Swivel radius | 4.07 in |
| Swivel interference | 8.15 in |

FITTING

| | |
|--------------------|--|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.43 in |
| Hint | Castors can be mounted with standard screws of any length. |

AGILA

2470PIO125P30-11

EAN 4031582361100
Order number 00062870



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

