

# AGILA TWIN

2977PJO050P30 TFR

EAN 4031582386431



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila twin                    |
| Type                        | Swivel caster with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 1.8 mph    | 154.32 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 308.65 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 2.72 in                       |
| Overall weight              | 0.58 lb                       |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Twin wheel housing  |
| Swivel bearing      | Two ball races      |
| Offset              | 0.98 in             |
| Swivel radius       | 3.9 in              |
| Swivel interference | 7.8 in              |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | Without threadguard  |
| Diameter              | 1.97 in              |
| Tread width           | 0.75 in              |
| Hardness of tread (A) | 87 Shore A           |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 0.43 in   |