

# AGILA

2478PJP075P40

EAN 4031582452761



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Load capacity Static	330.69 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.94 in
Overall weight	0.44 lb

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Broad

## FITTING

Fitting type	Square plate
Plate length	2.64 in
Plate width	2.36 in
Plate hole length (Minimum)	1.57 in
Plate hole length (Maximum)	1.89 in
Plate hole width (Minimum)	1.57 in
Plate hole width (Maximum)	1.89 in
Plate hole diameter	0.25 in

# AGILA

2478PJP075P40

EAN 4031582452761



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

