

AGILA US

2675PJP5X1.25P30-13

EAN 4031582435870



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-------------------------|--|
| Product name | Agila US |
| Housing type | Swivel castor with wheel brake |
| Standard | Institute of Casters and Wheel Manufacturers |
| Load capacity at 3 km/h | 125 kg |
| Load capacity Static | 250 kg |
| Overall height | 155 mm |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 127 mm |
| Tread width | 31.75 mm |
| Axle hole diameter | 10 mm |
| Hardness of tread (A) | 77 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Broad, reinforced |
| Swivel bearing | Two ball races |
| Offset | 37 mm |
| Swivel radius | 118.5 mm |
| Swivel interference | 237 mm |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 13 mm |