

# LUMINA

5525UOI075L51-11 RAL9006

EAN 4031582310696  
Order number 00073425



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	88 mm
Overall width	65 mm
Overall weight	0.295 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	10 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Colour	White aluminium (RAL9006)
Offset	30 mm
Swivel radius	106 mm
Swivel interference	212 mm
Dome diameter	45 mm

## FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	11 mm

PRODUCT INFORMATION

# LUMINA

5525UOI075L51-11 RAL9006

EAN 4031582310696  
Order number 00073425



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

