

# AGILA

2477DYK075P30-11

EAN 4031582335019  
Order number 00004957



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	121.25 lb
Load capacity Static	242.51 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	3.94 in
Overall width	1.69 in
Overall weight	0.88 lb

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black, electric-conductive
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	0.94 in
Swivel radius	3.15 in
Swivel interference	6.3 in
Dome diameter	1.69 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in
Hint	Castors can be mounted with standard screws of any length.

# AGILA

2477DYK075P30-11

EAN 4031582335019  
Order number 00004957



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

