

AGILA LIGHT

1477PA0075P30-11 TENTE

EAN 4031582338492
Order number 00900450



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila light
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	132.28 lb
Load capacity Static	264.55 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.94 in
Overall width	1.73 in
Overall weight	0.54 lb

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, injected
Bearing	Plain bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	91 Shore A
Hardness of tread (D)	40 Shore D

HOUSING

Material	Steel sheet, light
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	0.98 in
Swivel radius	3.07 in
Swivel interference	6.14 in
Dome diameter	1.61 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in

PRODUCT INFORMATION

AGILA LIGHT

1477PAO075P30-11 TENTE

EAN 4031582338492
Order number 00900450



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

