

# AGILA

2470DIK125R05-28

EAN 4031582300659



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila                     |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 100 kg                    |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 200 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 80 °C                     |
| Overall Height              | 163 mm                    |
| Overall width               | 60 mm                     |
| Overall weight              | 1.31 kg                   |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel Bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 41 mm               |
| Swivel radius       | 103.5 mm            |
| Swivel interference | 207 mm              |
| Dome diameter       | 60 mm               |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Sheet Steel               |
| Tread Material Mix    | Solid rubber, non-marking |
| Bearing               | Cone ball bearing         |
| Wheel Color           | Blue passivated           |
| Threadguards          | With threadguard          |
| Diameter              | 125 mm                    |
| Tread width           | 32 mm                     |
| Body width            | 32 mm                     |
| Hardness of tread (A) | 80 Shore A                |

## FITTING

|                              |                   |
|------------------------------|-------------------|
| Fitting type                 | Solid stem, round |
| Bolt diameter                | 28 mm             |
| Bolt length                  | 45 mm             |
| Bolt thread position         | 19 mm             |
| Bolt mounting holes quantity | 2                 |

# AGILA

2470DIK125R05-28

EAN 4031582300659

Order number 00006786  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

