

LINEA LIGHT

5920PJI075P41-38X38 RAL7001

EAN 4031582456158



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product name | Linea light |
| Housing type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 132.28 lb |
| Load capacity Static | 264.55 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 3.37 in |
| Overall width | 2.17 in |
| Overall weight | 0.3 lb |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Threadguards | Without threadguard |
| Diameter | 2.95 in |
| Tread width | 0.59 in |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|--------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Offset | 0.91 in |
| Swivel radius | 2.56 in |
| Swivel interference | 5.12 in |
| Dome diameter | 1.18 in |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 1.5 in |
| Plate width | 1.5 in |
| Plate hole length (Maximum) | 1.06 in |
| Plate hole width (Maximum) | 1.06 in |
| Plate hole diameter | 0.2 in |



LINEA LIGHT




5920PJI075P41-38X38 RAL7001

EAN 4031582456158



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award