

STYLEA

5925YGI065S70-M10X15 DOM23

EAN 4031582438765



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stylea
Type	Accessory
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	110.23 lb
Electric conductive	✓
Load capacity Static	220.46 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.91 in
Overall width	1.65 in
Overall weight	0.31 lb

WHEEL

Axle	Riveted
Diameter	2.56 in
Tread width	0.28 in
Hardness of tread (A)	87 Shore A

FITTING

Stem diameter	0.39 in
Stem length	0.59 in