

# AGILA TWIN

2975DIK050P30-11

EAN 4031582302783  
Order number 00030577



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	69 mm
Overall width	57 mm
Overall weight	0.362 kg

## WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	80 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	25 mm
Swivel radius	77 mm
Swivel interference	155 mm
Dome diameter	53 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

# AGILA TWIN

2975DIK050P30-11

EAN 4031582302783  
Order number 00030577



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

