

LINEA LIGHT

5925UAP075L51-10 RAL7001 RAL7015-std-brake-lever English

EAN 4031582453928



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ● ○ ○ |
| Movement Noise | ● ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product Name | Linea light |
| Type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall Height | 75.5 mm |
| Overall width | 55 mm |
| Overall weight | 0.2 kg |

HOUSING

| | |
|---------------------|-----------------------|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel Bearing | Stem, swiveling |
| Housing Color | Silver grey (RAL7001) |
| Offset | 23 mm |
| Swivel radius | 81 mm |
| Swivel interference | 162 mm |
| Dome diameter | 30 mm |

WHEEL

| | |
|--------------------|------------------------|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 75 mm |
| Tread width | 15 mm |

FITTING

| | |
|--------------------|--------------------|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 10 mm |



Deutscher
Designer
Club



Interzum
Award



product
design
award

IF Design
Award

LINEA LIGHT

5925UAP075L51-10 RAL7001 RAL7015-std-brake-lever English

EAN 4031582453928



BETTER MOBILITY. BETTER LIFE.

Product Drawings



Deutscher
Designer
Club



Interzum
Award



product
design
award

IF Design
Award