

FOOTMASTER

FOOT MASTER GD-120-F-NYN-CAL

EAN 4031582413267



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement Noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion Resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	1000 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1000 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	120 mm
Overall width	100 mm
Overall weight	1.8 kg

HOUSING

Housing Color	White
Offset	52 mm
Swivel radius	89 mm
Swivel interference	178 mm
Dome diameter	100 mm

WHEEL

Bearing	Roller bearing, damped
Wheel Color	Black
Diameter	75 mm
Tread width	30.5 mm
Body width	30.5 mm

FITTING

Plate length	95 mm
Plate width	95 mm
Plate hole length (Maximum)	70 mm
Plate hole width (Maximum)	70 mm
Plate hole diameter	11 mm

FOOTMASTER

FOOT MASTER GD-120-F-NYN-CAL

EAN 4031582413267

Order number 00062072
Product Drawings



BETTER MOBILITY. BETTER LIFE.

