

NOVATECH

FTP 100x50-Ø20 HL60

EAN 4031582329391



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Body material	Cast iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	100 mm
Tread width	50 mm
Axle Hole Diameter	20 mm
Hub Length	60 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	540 kg
Load capacity at 6 km/h	450 kg
Electric Conductive	No
Stainless	No
Load capacity Static	900 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.67 kg




PRODUCT INFORMATION

NOVATECH

FTP 100x50-020 H160

EAN 4031582389381

Order number 10801149



BETTER MOBILITY. BETTER LIFE.