

COMPACTA

1530POO040P41

EAN 4031582429220



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.09 in
Overall weight	0.22 lb

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.57 in
Hardness of tread (A)	95 Shore A

HOUSING

Material	Steel sheet, light
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	One ball race
Offset	0.67 in
Swivel radius	1.46 in
Swivel interference	2.91 in

FITTING

Fitting type	Square plate
Plate length	1.38 in
Plate width	1.38 in
Plate hole length (Maximum)	0.98 in
Plate hole width (Maximum)	0.98 in
Plate hole diameter	0.2 in