

# AGILA

2471PJP150P50

EAN 4031582301458



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Agila                               |
| Type                        | Swivel caster with directional lock |
| Standard                    | EN12530 - Devices Castors           |
| Load capacity at 1.8 mph    | 220.46 lb                           |
| Electric conductive         | no                                  |
| Stainless                   | no                                  |
| Load capacity Static        | 440.92 lb                           |
| Temperature range (Minimum) | -4 °F                               |
| Temperature range (Maximum) | 140 °F                              |
| Overall height              | 7.28 in                             |
| Overall weight              | 2.29 lb                             |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 1.42 in             |
| Swivel interference | 10.31 in            |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 5.91 in                |
| Tread width           | 1.26 in                |
| Hardness of tread (A) | 87 Shore A             |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 3.03 in           |
| Plate width                 | 2.64 in           |
| Plate hole length (Minimum) | 2.2 in            |
| Plate hole length (Maximum) | 2.42 in           |
| Plate hole width (Minimum)  | 1.83 in           |
| Plate hole width (Maximum)  | 2.03 in           |
| Plate hole diameter         | 0.33 in           |

# AGILA

2471PJP150P50

EAN 4031582301458



BETTER MOBILITY. BETTER LIFE.

Product Drawings

