

# STYLEA

5925UOI035L51-10 9011/9011/9011

EAN 4031582371055  
Order number 00770423



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	45 mm
Overall width	52 mm
Overall weight	0.055 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	35 mm
Tread width	12 mm
Body width	12 mm

## HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Colour	Graphite black (RAL9011)
Offset	12 mm
Swivel radius	45 mm
Swivel interference	90 mm
Dome diameter	15.2 mm

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm

# STYLEA

5925UOI035L51-10 9011/9011/9011

EAN 4031582371055  
Order number 00770423



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

