

PRODUCT INFORMATION

NOVATECH

FTP 400x80-Ø40 HL90

EAN 4031582319507



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES


Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	6613.86 lb
Load capacity at 3.7 mph	5511.55 lb
Electric conductive	no
Stainless	no
Load capacity Static	11023.1 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	52.02 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	15.75 in
Tread width	3.15 in
Axle hole diameter	1.57 in
Hub length	3.54 in
Body width	3.15 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D




PRODUCT INFORMATION

NOVATECH

FTP 400x80-040 H290

EAN 4031582319507

Order number 10802486



BETTER MOBILITY. BETTER LIFE.