

DELTA TWIN

9940ETP065P41-100X100

EAN 4031582501162
Order number 00800241



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Delta twin
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	60 °C
Overall height	111.5 mm
Overall width	92 mm
Overall weight	1.932 kg

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	65 mm
Tread width	30 mm
Body width	30 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material fork	Iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Colour	Transparent coating
Offset	25 mm
Swivel radius	62 mm
Swivel interference	124 mm
Dome diameter	73 mm

FITTING

Fitting type	Square plate
Plate length	100 mm
Plate width	100 mm
Plate hole length (Minimum)	63 mm
Plate hole length (Maximum)	78 mm
Plate hole width (Minimum)	63 mm
Plate hole width (Maximum)	78 mm
Plate hole diameter	10.5 mm

DELTA TWIN

9940ETP065P41-100X100

EAN 4031582501162
Order number 00800241



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

