

# LINEA LIGHT

5920PJ1065L51-10

EAN 4031582403947



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product name                | Linea light                 |
| Type                        | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph    | 88.18 lb                    |
| Load capacity Static        | 176.37 lb                   |
| Temperature range (Minimum) | 14 °F                       |
| Temperature range (Maximum) | 104 °F                      |
| Overall height              | 2.68 in                     |
| Overall width               | 1.81 in                     |
| Overall weight              | 0.2 lb                      |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Threadguards          | Without threadguard            |
| Diameter              | 2.56 in                        |
| Tread width           | 0.55 in                        |
| Hardness of tread (A) | 87 Shore A                     |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material            | Polyamide          |
| Fork shape          | Twin wheel housing |
| Swivel bearing      | Stem, swiveling    |
| Swivel radius       | 2.2 in             |
| Swivel interference | 4.41 in            |
| Dome diameter       | 0.91 in            |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 0.39 in                    |



# LINEA LIGHT

5920PJI065L51-10

EAN 4031582403947



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award