

# LINEA LIGHT

5927UAO075S70-M10X15 KP HN EN12528 RAL7001

EAN 4031582415087



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor with total lock
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	86 mm
Overall width	55 mm
Overall weight	0.215 kg

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	15 mm

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	23 mm
Swivel radius	82 mm
Swivel interference	164 mm
Thread diameter	0 mm

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	15 mm



PRODUCT INFORMATION

# LINEA LIGHT

5927UAO075S70-M10X15 KP HN EN12528 RAL7001


EAN 4031582415087



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award