

# AGILA CARE

2474YGO125R36-32S30 4xM6

EAN 4031582342093



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                                       |
|-----------------------------|-------------------------------------------------------|
| Product Name                | Agila care                                            |
| Type                        | Swivel castor with central, total or directional lock |
| Standard                    | EN12530 - Devices Castors                             |
| Load capacity at 3 km/h     | 100 kg                                                |
| Electric Conductive         | Yes                                                   |
| Stainless                   | No                                                    |
| Load capacity Static        | 200 kg                                                |
| Temperature range (Minimum) | -20 °C                                                |
| Temperature range (Maximum) | 60 °C                                                 |
| Overall Height              | 163 mm                                                |
| Overall weight              | 0.9 kg                                                |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel Bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 41 mm               |
| Swivel radius       | 103.5 mm            |
| Swivel interference | 207 mm              |

## WHEEL

|                       |                                           |
|-----------------------|-------------------------------------------|
| Body material         | Polypropylene, electric conductive        |
| Tread Material Mix    | Thermoplastic rubber, electric-conductive |
| Bearing               | Plain bearing                             |
| Threadguards          | Without threadguard                       |
| Diameter              | 125 mm                                    |
| Tread width           | 32 mm                                     |
| Hardness of tread (A) | 87 Shore A                                |

## FITTING

|               |                                                    |
|---------------|----------------------------------------------------|
| Brake cam     | hex cam                                            |
| Fitting type  | Stem with cam hole for profile bars, short version |
| Bolt diameter | 32 mm                                              |
| Bolt length   | 51 mm                                              |

# AGILA CARE

2474YGO125R36-32S30 4xM6

EAN 4031582342093



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

---

