

# AGILA

2477PJO150R05-28 M8/19

EAN 4031582302073  
Order number 00063769



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	188 mm
Overall width	60 mm
Overall weight	1.161 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	150 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	36 mm
Swivel radius	131 mm
Swivel interference	262 mm
Dome diameter	60 mm

## FITTING

Fitting type	Solid stem, round
Bolt diameter	28 mm
Bolt length	45 mm
Bolt thread position	19 mm
Bolt mounting holes quantity	2

# AGILA

2477PJO150R05-28 M8/19

EAN 4031582302073  
Order number 00063769



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

