

# LUMINA

6A23YOI050B10-11X20/10 RK. SCHWARZ

EAN 4031582340556  
Order number 00073825



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor with intermittend brake
Electric conductive	✓
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.32 in
Overall width	2.17 in
Overall weight	0.28 lb

## WHEEL

Body material	Polypropylene, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.31 in
Body width	0.31 in
Hardness of tread (D)	65 Shore D

## HOUSING

Material	Zinc-die-casting / Aluminum
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Swivel radius	2.01 in
Swivel interference	4.02 in

## FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in

PRODUCT INFORMATION

# LUMINA

6A23YOI050B10-11X20/10 RK. SCHWARZ

EAN 4031582340556  
Order number 00073825



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

