

# KAPPA LOAD

9658MOP300P64

EAN 4031582478860



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Kappa load
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	2400 kg
Load capacity at 6 km/h	1800 kg
Load capacity Static	4800 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	355 mm
Overall weight	15.74 kg

## WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	300 mm
Tread width	80 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Lubrication nipple	✓

## FITTING

Fitting type	Large rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	140 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	15 mm

# KAPPA LOAD

9658MOP300P64

EAN 4031582478860

## TECHNICAL DRAWINGS

---

