

# STYLEA

5925UOI035L51-10 LH 9011/9011/9011

EAN 4031582356779



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Stylea                         |
| Type                        | Swivel caster with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 1.8 mph    | 110.23 lb                      |
| Electric conductive         | no                             |
| Stainless                   | no                             |
| Load capacity Static        | 220.46 lb                      |
| Temperature range (Minimum) | -4 °F                          |
| Temperature range (Maximum) | 140 °F                         |
| Overall height              | 1.3 in                         |
| Overall width               | 2.05 in                        |
| Overall weight              | 0.13 lb                        |

## HOUSING

|                     |                          |
|---------------------|--------------------------|
| Housing Material    | Polyamide                |
| Fork shape          | Twin wheel housing       |
| Swivel bearing      | Stem, swiveling          |
| Housing Color       | Graphite black (RAL9011) |
| Offset              | 0.47 in                  |
| Swivel radius       | 1.77 in                  |
| Swivel interference | 3.54 in                  |
| Dome diameter       | 0.6 in                   |

## WHEEL

|                |                                |
|----------------|--------------------------------|
| Body material  | Polyamide                      |
| Tread material | Identical with wheel body      |
| Bearing        | Plain bearing with spacer tube |
| Axle           | Riveted                        |
| Threadguards   | Without threadguard            |
| Diameter       | 1.38 in                        |
| Tread width    | 0.47 in                        |
| Body width     | 0.47 in                        |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 0.39 in                    |

# STYLEA

5925UOI035L51-10 LH 9011/9011/9011

EAN 4031582356779

Order number 00770069  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

