

# AGILA

2470UAP100R47-27-30

EAN 4031582325621



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	138 mm

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (D)	40 Shore D

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	38 mm
Swivel radius	88 mm
Swivel interference	176 mm

## FITTING

Fitting type	Synthetic expander, square
Expander fitting (Minimum)	27 mm
Expander fitting (Maximum)	30 mm
Hint	Please indicate required tube innerdiameter when ordering.

# AGILA

2470UAP100R47-27-30

EAN 4031582325621



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

