

# KAPPA

9688IEP125P63 CL67

EAN 4031582316407  
Order number 00828000



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Kappa
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	170 mm
Overall width	98 mm
Overall weight	3.325 kg

## WHEEL

Body material	Aluminium
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Jet black (similar RAL9005)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	68 Shore A

## HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Colour	Blue passivated
Lubrication nipple	✓
Dome diameter	96 mm

## FITTING

Fitting type	Medium rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

# KAPPA

9688IEP125P63 CL67

EAN 4031582316407  
Order number 00828000



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

