

COMPACTA

1430PJ1032P60-38x32

EAN 4031582415063



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Compacta
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	42.5 mm
Overall width	26 mm
Overall weight	0.05 kg

HOUSING

Housing Material	Steel sheet, light
Fork shape	Broad
Swivel Bearing	One ball race
Housing Color	Blue passivated
Offset	11 mm
Swivel radius	27 mm
Swivel interference	54 mm
Dome diameter	26.5 mm
Thread diameter	0 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	32 mm
Tread width	15 mm
Body width	15 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	38 mm
Plate width	32 mm
Plate hole length (Maximum)	24 mm
Plate hole width (Maximum)	30 mm
Plate hole diameter	4.2 mm
Stem length	15 mm

COMPACTA

1430PJI032P60-38x32

EAN 4031582415063



BETTER MOBILITY. BETTER LIFE.

Product Drawings

